



## **Időjárásálló üvegszálás készülékház, 111,12 cm x 111,12 cm x 127 cm**

|                              |                |
|------------------------------|----------------|
| <b>Termékszám:</b>           | <b>6994</b>    |
| HUF Ár (nettó):              | Elérhetőségünk |
| Szállítási dátum nem látható |                |

### **Optimize your equipment's life by protecting it from the elements.**

Ez a készülékház egy hűtött mintavevőt képes befogadni.

Külső méretek: 43,75"Szé x 43,75"Mé x 50"Ma.

Belső méretek: 35,75"Szé x 35,75"Mé x 49"Ma

Ajtónyílás: 29"Szé x 44"Ma

### **Tough, locking Weatherguard Enclosures are ideal for housing samplers, pumps, switch gear, and transformers**

implified keypad with intuitive icons and scrolling menu of the Hach Sigma SD900 Active Cooling Sampler assures easy setup. The large 5-line transreflective LED backlit display is readable in bright or subdued lighting.

### **One-piece molded, fiberglass-reinforced plastic**

Worried about replacing tubing? The peristaltic pump with spring loaded rollers reduces pump tubing wear and prevent pump jams. The life time of pump tubing is 20,000 cycles compared to 1000 cycles on other samplers.

### **Insulated and gasketed**

Do you need samples to meet local regulations of 24 x hourly mixed / daily mixed sample?

We offer unique options of 1 x 25 litre PE and 1 X 20 litre glass with an active cooled sampler base.

### **Designed to withstand winds of 130 mph**

The compact, weather-proof housing polyethylene plastic ensures failure-free operation over many years even in extremely corrosive applications.

### **Accurate sampling for correct analysis**

The Sigma SD900 Portable Active cooling sampler comes with an integrated cooling machine which includes an autarktic temperature control for accurate temperature controlled sample conservation.