



A1100 O₂ sensor, ATEX, hastelloy, FFKM/FFPM O-rings, cap w/o grille; ATEX certified only when used with an ATEX 36xxEx instrument

Termékszám:

A110E-HKS

ELAVULT CIKK

Ez a termék már nem elérhető.

Műszaki adatok

A doboz tartalma:

Sensor only.

Controller, sensor cable, flow-chamber or process connection must be ordered separately.

Anyag:

O-Rings: FFKM/FFPM

Áramlási sebesség:

Recommended flow rate in flow chamber

2935A-A : 25 mL/min

2952A-A : 50 mL/min

2956A-A : 180 mL/min

29552A-A : 50 mL/min

Body Material:

Hastelloy

Garancia:

24 hónap

Hőmérséklet tartomány:

-5 - 60 °C (23 - 140 °F), without grille, during measurement or

-5 - 95 °C (23 - 203 °F), with grille

Környezeti hőmérséklet:

-5 - 100 °C (23 - 212 °F) (due to electrolyte, but sensor will not be damaged up to 200°C / 392°F) (mechanical)

Méréstartomány:

Range at 25 °C

2935A-A: 10 ppb - 400 ppm or 20 Pa - 1,000 kPa

2952A-A: 1 ppb - 80 ppm or 5 Pa - 200 kPa

2956A-A: 0.1 ppb - 20 ppm or 0.25 Pa - 50 kPa

29552A-A: 2 ppb - 80 ppm or 5 Pa - 200 kPa

Minta: nyomás:

0 - 100 bar

Nedvesített anyagok:

Stainless Steel 1.4404 (AISI 316L), surface finish: N5, Ra < 0.4 µm

Membrane (see specification table).

	No O-rings are in contact with the sample.
Precizitás (RDS):	$\pm 1\%$ of reading, or $\pm$ lower measurement range, whichever is greater
Súly:	0,3 kg
Tanúsítványok:	2004/108/EC - EN 61326-1
Válaszidő :	2935A-A : 2,5 min
	2952A-A : 38 s
	2956A-A : 7,2 s
	29552A-A : 90 s
Védettségi osztály:	IP68

A doboz tartalma

Sensor only. Controller, sensor cable, flow-chamber or process connection must be ordered separately.