



Hach 934-AH Filters, 125mm, 100/pk

Termékszám:	2511212
HUF Ár (nettó):	Elérhetőségünk
Szállítási dátum nem látható	

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5 µm particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

934-AH is a registered trademark of Whatman, Inc./GE Healthcare and used under license.

Műszaki adatok

Anyag:	Glass Microfiber
Átmérő:	125 mm
Egység:	100/pk
Szemcseméret:	1.5 µm
Térfogat/ csomagméret:	100 /pk